



Q-Series OFP Standard Density Adapter Panels offer pass-through connections and front-loading access for Q-Series Enclosures. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures.

Features & Benefits

Up to 72 LC fibers per RU	Available in, LC, SC, ST and blank styles
Made of durable polycarbonate	Zirconia ceramic sleeves for optimal performance
6, 8, 12 & 24 port panels	Color options available

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875968924	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	16
Simplex/Duplex	Duplex	Single/Multimode	Single-Mode