



Q-Series OFP Standard Density Adapter Panels offer pass-through connections and front-loading access for Q-Series Enclosures. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures. Available in LC, SC, ST & MPO adapters.

Features & Benefits

- Small footprint: Up to 72 LC fibers per RU Adapter panels available with a wide variety of configurations: Available in, LC, SC, ST and blank styles
- Plunger/grommet fasteners: Made of durable polycarbonate Front loading: Zirconia ceramic sleeves for optimal performance
- Fiber port labeling: 6, 8, 12 & 24 port panels Engineered polymer adapter panel: Color options available

Specifications

General Info

Product Line	Ortronics	Color	Green
UPC Number	662875631859	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	12
------------------------	-----	-----------------	----

Simplex/Duplex

Duplex

Single/Multimode

Single-Mode

Form Factor

SC Duplex
