



Ortronics
Q-Series OFP Adapter Panel 6-SC Simplex aqua adapters
Part No. OFP-SCS06LC



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

Up to 72 LC fibers per RU

Available in, LC, SC, ST and blank styles

Made of durable polycarbonate

Zirconia ceramic sleeves for optimal performance

6, 8, 12 & 24 port panels

Color options available

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875629207	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	6
Simplex/Duplex	Duplex	Single/Multimode	Single-Mode