



## Cablofil 5" Itray Aluminum Straight Sections

Part No. P300483



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

### Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

### Specifications

#### General Info

Product Line	Cablofil	Finish	AL
UPC Number	800388063488	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Straight Sections		

#### Dimensions

Product Width US	7.5 in	Product Weight US	17.5 lb
Product Volume US	2.688 cu ft	Product Depth US	120.0 in
Product Height US	5.16 in	Rung Spacing	6 in

#### Trade Programs

---

BAA	Yes
-----	-----

---

### Technical Information

---

NEMA Load Class	12C
-----------------	-----

---