




Cablofil  
LD-4A-90VI24-06 AL 4H 90° IVR 24R 06W (TRA)  
Part No. P302840



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Includes splices and hardware

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388087064	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Vertical Elbows		

### Dimensions

Product Width US	7.5 in	Product Weight US	10.184 lb
Product Volume US	4.171 cu ft	Product Depth US	31.0 in
Product Height US	31.0 in	Radius	24 in

### Trade Programs

BAA	Yes
-----	-----