




Cablofil
Vertical Hanger Splice Kit
Part No. P314200



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 5052 - H32

Finish: Plain

Height (H): Tray height: 4", 5", 6", 7" (less 1/2")

Torque: 19 - 25 ft-lbs

Supports vertical tray using threaded rod (not shown)

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|----------|
| Product Line | Cablofil | Finish | Aluminum |
| UPC Number | 800388200777 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Type | Splicing |

Dimensions

| | | | |
|-------------------|-------------|-------------------|----------|
| Product Width US | 3.143 in | Product Weight US | 2.382 lb |
| Product Volume US | 0.069 cu ft | Product Depth US | 6.502 in |
| Product Height US | 5.875 in | | |

Trade Programs

| | |
|-----|-----|
| BAA | Yes |
|-----|-----|