



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Steel

Finishes: ZN, PE, GC, 316L

Width: 1-1/2"

Load Rating: 1,200 lbs/pr (S.F.: 3X)

Threaded Rod Size: 3/8" or 1/2"

Kit Includes: 8 SFHN

## Specifications

### General Info

Product Line	Cablofil	Finish	Electro-Galvanized Steel
UPC Number	800388247826	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Accessories

### Dimensions

Product Width US	3.3 in	Product Weight US	1.521 lb
Product Volume US	0.012 cu ft	Product Depth US	3.7 in
Product Height US	1.7 in		