




Cablofil
Horizontal Adjustable Splice Kit
Part No. P322282



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Bend plates to appropriate angle as needed

Torque: 19ft./lbs.

KIT INCLUDES ONE INSIDE AND OUTSIDE PLATE

Field drill outer plate if needed

MEETS CABLE TRAY BONDING REQUIREMENTS

Specifications

General Info

Product Line	Cablofil	Finish	Custom Painted
UPC Number	800388524194	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Splicing

Dimensions

Product Width US	1.818 in	Product Weight US	2.666 lb
Product Volume US	0.159 cu ft	Product Depth US	39.0 in
Product Height US	3.875 in		

Trade Programs

BAA	Yes
-----	-----