



Ortronics
Discontinued - Palo Alto PAN-SFP-BX-U-40 Compatible 1000Base-BX SFP Transceiver (SMF, Tx: 1310nm Rx: 1490nm, 40km, LC Duplex, DDM, I-Temp)
Part No. PAN-SFP-BX-U-40-L

Palo Alto PAN-SFP-BX-U-40 Compatible 1000Base-BX SFP Transceiver (SMF, Tx: 1310nm Rx: 1490nm, 40km, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

| | | | |
|-------------------|-------------|---------------|--------------|
| Product Line | Ortronics | UPC Number | 662875070313 |
| Country Of Origin | China | Warranty Type | Lifetime |
| Type | Transceiver | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 13.4 mm | Product Depth US | 56.6 mm |
| Product Height US | 8.5 mm | | |

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-------|
| Fiber Optic Cable Type | Single-Mode | Max Distance Support | 40 km |
| Operating Temperature Min | -40 °C | Operating Temperature Max | 85 °C |
| Connector Type | LC Duplex | | |