



Clarity 6 angled 48-port high density Category 6 patch panel utilizes an innovative recessed angle design for a lower mounted profile. This Clarity 6 patch panel is component compliant to TIA/EIA Category 6 performance requirements. It occupies one rack unit, and measures 19" x 3.5". Jacks are grouped in six-port modules. It is part of the Clarity 6 link and channel solution that provides significant installed performance headroom.

## Features & Benefits

Recessed design with lower mounted profile: Directs cords more easily to vertical management.	ETL verified to TIA Category 6 component spec: Elevated component performance.
Center tuned to Clarity 6 patch cords: More transparent mated union.	Universal wiring: Supports T568A and T568B installs.
Easy lace 110 termination: Saves installation time.	Supplied rear cable management: Supports good cabling practice.
High density design: Maximizes rack utilization.	RoHS compliant: Lead free.

## Specifications

### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875497226	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Panel		

### Dimensions

Product Width US	19.0 in	Product Depth US	6.1 in
Product Height US	3.5 in		

### Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

### Technical Information

---

Category Performance Rating	Cat6	Compatibility	HDJ
-----------------------------	------	---------------	-----

---

Rack Units	1	Wire Gauge	22 AWG
------------	---	------------	--------

---

Number of Ports	48	Shielded/Unshielded	Shielded
-----------------	----	---------------------	----------

---

Connector Type	RJ-45	Wattage	100 W
----------------	-------	---------	-------

---

Voltage	60.0 V		
---------	--------	--	--

---