



Ortronics

Clarity Cat6a 24 port angled panel - 110/6port - T568A/B - 1.75 x 19 - HD

Part No. PHA6AU24



Clarity 6A 24-Port Angled Patch Panel is component compliant to EIA/TIA Category 6a performance requirements. High density design occupies 1 rack unit, measuring 19" x 1.75". Jacks are grouped in six-port modules. Part of the Clarity 6A link and channel solution that provides significant installed performance headroom.

Features & Benefits

CAT6A Compliant: Meets TIA 568C.2 Category 6A component specifications

Universally wired 110 termination: Supports T568A and T568B installs.

Supplied rear cable management: Supports good cabling practices

Angled recessed design with lower mounted profile: Directs cords more easily to vertical management.

High density design: Maximizes rack utilization.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875857495	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Panel		

Dimensions

Product Width US	19.0 in	Product Depth US	6.1 in
Product Height US	1.75 in		

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Product Environmental Profile Yes

Technical Information

Category Performance Rating	Cat6a	Compatibility	HDJ
Rack Units	1	Wire Gauge	22 AWG
Number of Ports	24	Shielded/Unshielded	Shielded
Connector Type	RJ-45	Wattage	100 W
Voltage	60.0 V		
