



Clarity 6 48-port high density Category 6 patch panel is component compliant to EIA/TIA Category 6 performance requirements. It occupies two rack units, and measures 19" x 3.5". Jacks are grouped in six-port modules. Part of the Clarity 6 link and channel solution that provides significant installed performance headroom.

Features & Benefits

ETL verified to TIA Category 6 component spec: Ensures component performance.

Universally wired 110 termination: Supports T568A and T568B installs.

Supplied rear cable management: Supports good cabling practice.

RoHS compliant: Lead free.

Center tuned to Clarity 6 patch cords: More transparent mated union.

New IDC housing: Handles larger Category 6 conductors.

High density design: Maximizes rack utilization.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875441274	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Panel		

Dimensions

Product Width US	19.0 in	Product Depth US	4.47 in
Product Height US	3.5 in		

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Product Environmental Profile	Yes		

Technical Information

Compatibility	HDJ	Rack Units	2
Wire Gauge	22 AWG	Number of Ports	48
Shielded/Unshielded	Shielded	Connector Type	RJ-45
Wattage	100 W	Voltage	60.0 V