

Light Duty, Standard Length, Flexible Eye. Cable Diameter - 1.000-1.240-inch, Mesh Length - 20-inch, Break Strength - 7,500 lbs.



## Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 20

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007993080
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	1 in	Minimum Cable Range	1.24 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations