



Pass and Seymour
Medium Duty, Flexible Eye
Part No. PM150

Medium duty, Flexible eye. Cable diameter - 1.500-1.740-inch, Mesh Length - 36-inch, Break Strength - 8,100 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007993585
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	1.5 in	Minimum Cable Range	1.74 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations