



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM1502

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 1.500-1.990-inch, Mesh Length - 36-inch, Eye Diameter - 7/16-inch, Break Strength - 16,400 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36: Eye Diameter: 7/16

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185164
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	1.5 in	Minimum Cable Range	1.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations