



Ortronics

Clarity 6 12-port Category 6 mini patch panel on 89 D bracket - 10 in x 2.3 in

Part No. PMP61289



Clarity 6 12-Port Category 6 mini patch panel is component compliant to EIA/TIA Category 6 performance requirements. Its high density design on a supplied 89D bracket maximizes wall space in small or confined locations. It measures 10" x 2.5". Jacks are grouped in six-port modules. Part of the Clarity 6 link and channel solution that provides significant installed performance headroom.

## Features & Benefits

ETL verified to TIA Category 6 component spec: Ensures component performance. Center tuned to Clarity 6 patch cords: More transparent mated union.

Universally wired 110 termination: Supports T568A and T568B installs. New IDC housing: Handles larger Category 6 conductors.

Supplied rear cable management: Supports good cabling practice. High density design: Maximizes rack utilization.

RoHS compliant: Lead free.

## Specifications

### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875462460	Country Of Origin	United States
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Panel		

### Dimensions

Product Width US	10.0 in	Product Depth US	1.86 in
Product Height US	2.3 in		

### Additional Information

---

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

---

### Technical Information

---

Category Performance Rating	Cat6	Wire Gauge	22 AWG
-----------------------------	------	------------	--------

---

Number of Ports	12	Shielded/Unshielded	Unshielded
-----------------	----	---------------------	------------

---

Wattage	100 W	Voltage	60.0 V
---------	-------	---------	--------

---