



Pass and Seymour
Heavy Duty, Standard Length, Rotating Eye, K-Type
Part No. PS1502

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 1.500-1.990-inch, Mesh Length - 34-inch, Eye Diameter - 1 3/8-inch, Break Strength - 16,400 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 34: Eye Diameter: 1-3/8

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007994391 |
| Country Of Origin | Mexico | Construction | Support and Strain Relief Grips, Various Types of Pulling |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1.5 in | Minimum Cable Range | 1.99 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |