

2-Pole Toggle Switch, Back and Side-Wire, 15A 120/277V



## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007195095
Country Of Origin	Mexico	Switch Type	Toggle
Number of Switches	1	Application Sector	Industrial

---

Standard

UL 20, FEDSPEC

Type

Switch

---

### Dimensions

---

Product Width US

1.32 in

Product Depth US

1.073 in

---

Product Height US

3.281 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber

140597

cULus Listed

Yes

---

### Technical Information

---

Contact Rating

15Amp, 120/277Vac

Amperage

15 A

---

Number of Poles

Double Pole

Wire Size

#14 - #10 AWG

---

Wattage

2 W

Voltage

120/277 V

---