



Pass and Seymour  
Extra Heavy Duty Spec. Grade and Security Switches  
Part No. PS20AC4KL



4-Way Key Lock Back and Side-Wire 20A 120/277V

## Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc.

Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Finish	Matte
UPC Number	785007195682	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 20, FEDSPEC
Type	Switch		

### Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

## Technical Information

---

Amperage	20 A	Number of Poles	4-Way
Wire Size	#14 - #10 AWG	Wattage	4 W
Voltage	120.0 V		

---