



Pass and Seymour  
Heavy Duty, Short Length, Rotating Eye, K-Type  
Part No. PS3001

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 3.00-3.490-inch, Mesh Length - 30-inch, Eye Diameter - 1 7/8-inch, Break Strength - 48,000 lbs.



## Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 30: Eye Diameter: 1-7/8

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007994155
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	3 in	Minimum Cable Range	3.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations