



Pass and Seymour
Replacement Switch with Auxiliary Contact, 30A
Part No. PS30RSAX

30A Replacement Switch with Auxiliary Contact



Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007243673
Country Of Origin	United States	Application Sector	Industrial
Type	Switch		

Dimensions

Product Width US	7.38 in	Product Depth US	4.88 in
Product Height US	9.69 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Horsepower Rating	10 HP @ 3 ϕ 240 VAC, 1-1/2 HP @ 120 VAC, 20 HP @ 3 ϕ 480 VAC, 20 HP @ 3 ϕ 600 VAC, 3 HP @ 208 VAC, 5 HP @ 277 VAC, 7-1/2 HP @ 480 VAC	Connection	Hardwired
Amperage	30 A	Enclosure Type	Not included.

Wire Size	#14 - #10 AWG	Maximum Horsepower Rating	50 HP @ 3ØY 347/600 VAC
-----------	---------------	---------------------------	----------------------------

Voltage	120 to 600 V
---------	--------------
