



Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS3501



Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 32-inch, Eye Diameter - 1 7/8-inch, Break Strength - 48,000 lbs.

Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 32: Eye Diameter: 1-7/8

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994162
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations