



Canadian 3way Lock Switch, Back & Side Wire, 20amp 347volt, Gray

Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- High strength thermoplastic polycarbonate toggle.
- Locking support provides resistance to face and back body separation.
- Grounding terminal is standard.
- Strap nickel-plated steel with integral ground.
- For covering patents, see www.legrand.us/patents.
- Heavy-duty bumper pads for quiet operation.
- Back body made of glass-reinforced nylon.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Shallow design for ease of installation.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007196405	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL 20

Technical Information

Actuator	Toggle	Contact Rating	20amp, 347vac
Amperage	20 A	Number of Poles	Double Pole