
Pass and Seymour
20A 3 Pole 4 Wire Fusible Mechanical Interlock
Part No. PS420FMIR5W



Three pole, Four wire, Fusible Mechanical Interlock Receptacle. 20 amp, 3/600 volt.

Features & Benefits

Top or Bottom feed.

End user decides at installation whether top or bottom feed is appropriate.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

Dimensions

Product Width US	9.13 in	Product Depth US	10.09 in
Product Height US	24.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Phase	3	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way
Voltage	480 V		