



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock. 20A, 3, 480V.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420432	Country Of Origin	United States
Number of Receptacles	1	Features	Adjustable Mounting Feet
Outlet Type	Pin & Sleeve	Application Sector	Industrial
Wall Plate Included	Yes	Standard	UL Listed
Warranty Type	1-Year		

Dimensions

Product Width US	9.13 in	Product Depth US	8.0 in
Product Height US	11.06 in		

Technical Information

Operating Temperature Min	-50 °C	Connection Location	Top and Bottom
Number of Wires	4	Operating Temperature Max	60 °C
Amperage	20 A	IEC Clock Position	Clock Position 7
Enclosure Type	NEMA 12, NEMA 4X	Number of Poles	3-Way
Indoor/Outdoor	Indoor	Operating Temperature	-50°-60°C
Wire Connection Type	Screw Terminals	Voltage	480.0 V
