



4-Pole, 5-Wire, Pin and Sleeve Receptacle. 100A, 3Y, 347/600V.

## Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions, and guaranteed IEC 309 compatibility.

Arrives ready to wire, with cord grip open and cable-ready. Terminal screws come backed out and ready to wire. Front and back body require no disassembly prior to assembly.

Nylon construction for high impact and corrosion resistance.

Nickel-plated brass pins provide extracorrosion resistance without sacrificing electrical conductivity.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Natural-rubber grommets provide watertight protection at cable entry.

Combination-head screws for added convenience and quick installation.

Revolutionary, hinged cord grip for durable performance and ease of installation.

Cover with integral neoprene gasket provides watertight seal.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007051087	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

### Dimensions

Product Width US	5.2 in	Product Height US	6.6 in
------------------	--------	-------------------	--------

---

Product Length US	5.6 in
-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	151348	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Number of Wires	5	Amperage	100 A
-----------------	---	----------	-------

---

Number of Poles	4-Way	Voltage	347.0 V
-----------------	-------	---------	---------

---