



Pass and Seymour
15A, 125V Extra-Hard Use Spec-Grade Plug, Black and Gray
Part No. PS5266XGRY



Straight Blade Plug 2-Pole 3-Wire 15A 125V Gray

Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Rugged two-piece cord grip provides more uniform cord retention.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see www.legrand.us/patents.

Nylon housing provides impact and chemical resistance.

Internal dust shield keeps terminals free of contaminants.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007236958	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC
Type	Straight Blade		

Dimensions

Product Width US	1.516 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Wires 3 Amperage 15 A

Number of Poles Double Pole Wire Size 18 - 10 AWG
