



4-Pole, 5-Wire, Non-Fusible Mechanical Interlock. 30A, 3Y, 277/480V.

Features & Benefits

- Top or Bottom feed. Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate. No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420531	Country Of Origin	United States
Number of Receptacles	1	Features	Adjustable Mounting Feet
Outlet Type	Pin & Sleeve	Application Sector	Industrial
Wall Plate Included	Yes	Standard	UL Listed
Warranty Type	1-Year		

Technical Information

Operating Temperature Min	-50 °C	Connection Location	Top and Bottom
Number of Wires	5	Operating Temperature Max	60 °C
Amperage	30 A	IEC Clock Position	Clock Position 7

Enclosure Type	NEMA 12, NEMA 4X	Number of Poles	4-Way
Indoor/Outdoor	Indoor	Operating Temperature	-50°-60°C
Wire Connection Type	Screw Terminals	Voltage	277.0 V
