



Straight Blade Connector 2-Pole 3-Wire 20A 125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see www.legrand.us/patents.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007237597	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL Listed, FEDSPEC
Type	Straight Blade		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

Technical Information

Number of Wires

3

Amperage

20 A

Number of Poles

Double Pole

Wire Size

18 - 10 AWG
