



Pass and Seymour
Sloped-Roof Stainless Steel Safety Switch, 60A HP
Part No. PSDS60HPSR



60 Amps HP Sloped-Roof Stainless Steel Safety Switch. Legrand's 316-Grade Sloped-Roof Stainless Steel Safety Switches are designed to provide superior corrosion resistance in harsh environments like food and beverage processing plants where wash down/hose down at extreme temperatures is a daily necessity, as well as environments where salts, acids, and chemicals are prevalent. Legrand's Sloped-Roof Stainless Steel Safety Switches with NEMA 4X/12, IP66, 67, and 69K ratings are the best solution for durability and personnel safety in any environment.

Features & Benefits

Type 316 grade stainless steel provides superior resistance to corrosion.

Certified by the National Sanitation Foundation (NSF) for hygiene requirements in food & beverage processing.

15: sloped roof helps to facilitate run-off and minimize the harborage of contaminants.

Water- and dust-tight enclosure rated NEMA 3R, 4, 4X, 12K and IP66, 67, 69 for protection against high-pressure, high-temperature water from multiple directions.

OSHA-compliant Lockout/Tagout.

Captive cover screws.

Inability to remove cover when in ON position.

6 conduit entry points for flexible installation options.

Can accommodate up to 3 sets of auxiliary contacts for control circuit applications.

3/4" standoffs on mounting feet allow adequate space for runoff and inspection behind the switch.

High-visibility yellow and red handle can be padlocked to meet OSHA lockout/tagout requirements.

Multiple drill points for ease of installation (each side and back).

No labels on cover, stamped-in ON/OFF.

Compact footprint.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007133660
Country Of Origin	United States	Application Sector	Industrial
Type	Safety Switch		

Dimensions

Product Width US	8.3 in	Product Depth US	7.1 in
------------------	--------	------------------	--------

Product Height US	14.03 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Horsepower Rating	15 HP @ 3 ϕ 240 VAC, 15 HP @ 480 VAC, 15 HP @ 600 VAC, 3 HP @ 120 VAC, 30 HP @ 3 ϕ 480 VAC, 30 HP @ 3 ϕ 600 VAC, 7-1/2 HP @ 240 VAC, 7-1/2 HP @ 277 VAC	Connection	Hardwired
-------------------	--	------------	-----------

Amperage	60 A	Enclosure Type	NEMA 12, NEMA 4X, Stainless Steel
----------	------	----------------	--

Wire Size	#14 - #10 AWG	Maximum Horsepower Rating	30 HP @ 3 ϕ 600VAC
-----------	---------------	---------------------------	----------------------------

Wiring Location	Bottom, Top	Voltage	120 to 600 V
-----------------	-------------	---------	--------------
