



15A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven **SafeLock® Protection** feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
- Faster, more reliable installation **No exposed terminals** create a finger-safe application before, during, and after installation
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector **GFCI works with the existing 3-wire PlugTail connectors** creating a non-feed-through application for facility
- Zinc-plated steel mounting strap

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007049060	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection	Built-in Connector
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Mounting Type	Box	Environmental Conditions	95% Humidity, UL 94 V2
