



15A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven

Faster, more reliable installation

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector

Zinc-plated steel mounting strap

SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

No exposed terminals create a finger-safe application before, during, and after installation

GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007048018	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection	Built-in Connector
Amperage	15 A	Number of Poles	Double Pole

Indoor/Outdoor

Indoor

Environmental Conditions

95% Humidity, UL 94 V2
