Pass and Seymour
**PlugTail® Single Pole 15A Toggle Switch, White**
Part No. PT15AC1W



PlugTail® Single-Pole 15A Toggle Switch

## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | cULus, WS8996 | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |

| | |
|---|---|
| Product Height US | 3.281 in |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 140597 | cULus Listed | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Contact Rating | 15amp, 120/277vac | Closed Contact Resistance | Toggle |
| Amperage | 15 A | Number of Poles | Single Pole |
| Wattage | 1 W | Voltage | 120 V |