



20A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the components are damaged and protection is lost, GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical power to the receptacle is disconnected

Faster, more reliable installation

No exposed terminals create a finger-safe application before, during, and after installation

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector

GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility

Zinc-plated steel mounting strap

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007048346
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Self-Test	Application Sector	Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor
----------------	--------
