Pass and Seymour

# PlugTail® Hospital Grade 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Ivory

Part No. PT2097HGI



PlugTail® Hospital-Grade 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | Commercial, GFCI, Indoor, Self-Test |
| Application Sector | Residential/Commercial | Standard | cULus, UL Listed, FSUL |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.72 in | Product Depth US | 1.2 in |
| Product Height US | 4.2 in | | |

### Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Interrupt Rating | 4 A | Frequency Rating | 60 Hz |
| Trip Range | 4 to 6 mA | Amperage | 20 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| Voltage | 125 V | | |