



Pass and Seymour

PlugTail® Hospital Grade Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Light Almond

Part No. PT2097HGTRLA



PlugTail® Hospital-Grade Tamper-Resistant 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

| | | | |
|-----------------------|----------------------------|-------------------|-----------------------------------|
| Product Line | Pass & Seymour | Color | Light Almond |
| UPC Number | 785007047837 | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | GFCI, Self-Test, Tamper-Resistant |
| Application Sector | Commercial, Hospital Grade | Standard | cULus, UL Listed, FSUL |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.72 in | Product Depth US | 1.2 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|--------|--------------------------|------------------------|
| Is Tamper-Resistant | Yes | Connection | Built-in Connector |
| Amperage | 20 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Environmental Conditions | 95% Humidity, UL 94 V2 |