Pass and Seymour
PlugTail® Specification Grade Illuminated 20A Toggle Switch, Clear
Part No. PT20AC1CSL



Single-Pole Illuminated Toggle Switch, 20A 120/277VFor detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece nickel-plated mounting strap for superior corrosion resistance

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

No exposed terminals create a finger safe application before, during, and after installation.

Glass-reinforced nylon back body for durability and strength.

Heavy-duty bumpers for quiet, smooth operation.

Shallow design for easier installation.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Clear
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 20		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Technical Information

Actuator	Toggle	Contact Rating	20amp, 120/277vac
Amperage	20 A	Action	DPDT
Number of Poles	Double Pole	Voltage	120 V