



Pass and Seymour  
**PlugTail® Single Pole 20A Decorator Switch, Gray**  
Part No. PT2621GRY



PlugTail® Single-Pole 20A Decorator Switch

## Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtailed

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007000689
Country Of Origin	Mexico	Features	Decorator Style
Application Sector	Industrial	Standard	UL 20
Type	Switch		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

---

Amperage

20 A

Number of Poles

Single Pole

---

Wire Size

#14 - #10 AWG

Voltage

120/277 V

---