



PlugTail® Isolated Ground Decorator Spec Grade Receptacles, 15A, 125A

Features & Benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
 - No exposed terminals create a finger safe application before, during, and after installation.
 - Crimped and welded contacts.
 - Large brass contacts snugly terminate on device blade terminals.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- Plated steel wrap strap design for maximum durability and corrosion resistance.
 - Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
 - Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
 - Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
 - For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007307757	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG		
-----------	-------------	--	--
