


PlugTail® Isolated Ground Heavy-Duty Hospital Grade Receptacles, 15A, 125A



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|-----------------|
| Product Line | Pass & Seymour | Color | Red |
| UPC Number | 785007278057 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL 498, FEDSPEC |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------|-------------|-----------------|-------------|
| Phase | Three | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | | |
