



Pass and Seymour  
**PlugTail® Connectors, Right Angle, Stranded, 6-in**  
Part No. PTR6STR



PlugTail® Connectors, Right Angle, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Plated steel wrap strap design for maximum durability and corrosion resistance.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007044546
Country Of Origin	China	Application Sector	Commercial
Standard	cULus UL498		

### Dimensions

---

Product Length US      6.0 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber      140596                      cULus Listed                      Yes

---

### Technical Information

---

Dielectric Strength      Withstands 2000V minimum      Temperature Rating              -40° - 60° C

---

Wire Size                      12 AWG

---