



Pass and Seymour
PlugTail® 3.1A Spec Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, Gray
Part No. PTTR15ACUSBGRY



PlugTail® Commercial Specification Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices – one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides all power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects

Triple-wipe, brass line contacts for 15A commercial applications

Zinc-plated steel for corrosion resistance

Stainless steel auto-ground clips assure positive ground

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Multiple color options available

5Vdc Type-C USB port to charge USB Type-C compatible mobile devices

Available in 15 & 20A, Specification Grade and Hospital Grade configurations

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007110098	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	USB-Charging	Application Sector	Commercial
Standard	FEDSPEC	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.45 in
------------------	----------	------------------	---------

Product Height US	2.677 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

USB Amperage	3.1 A	Number of USBs	2
--------------	-------	----------------	---

USB Power Output	15 W	Amperage	15 A
------------------	------	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------
