



Pass and Seymour
PlugTail® Tamper-Resistant Hospital Grade Receptacle, 15A, 125V, Ivory
Part No. PTTR26262HGI



PlugTail® Tamper-Resistant Hospital Grade Decorator Receptacle, 15 A 125 V, White. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects
 - Plated steel wrap strap design for maximum durability and corrosion resistance.
 - Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
 - Pre-stripped connector leads fasten to conductors, easier than standard pigtails
 - For covering patents, see www.legrand.us/patents.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
 - No exposed terminals create a finger safe application before, during, and after installation.
 - Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
 - PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007008685	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498, FEDSPEC

Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
------------------	--------	------------------	----------

Product Height US	2.6 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	12 AWG	Environmental Conditions	Flammability: UL94 V2
-----------	--------	--------------------------	-----------------------
