



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Prewired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

No exposed terminals create a finger-safe application before, during and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007001501
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Straight Blade, Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
------------------	--------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
---------------------------	--------	---------------------	-----

Connection Location	Back Only	Number of Wires	3
---------------------	-----------	-----------------	---

Operating Temperature Max	60 °C	Amperage	20 A
---------------------------	-------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
----------------	--------	-------------------------	-------

Operating Temperature	-40°-60°C	Number of Phases	3
-----------------------	-----------	------------------	---

Wire Connection Type	PlugTail	Voltage	125.0 V
----------------------	----------	---------	---------
