



Ortronics
PowerWise Cat5E solid cord Plenum, double ended 25ft, black
Part No. PW5EP25DB-00



PWC5E PowerWise Cat5E UTP solid 22 awg conductor plenum, double ended 25ft, black

Features & Benefits

Each cord is factory tested: Ensures every cord shipped meets Category 5e component specifications

Larger 22 awg conductors: Support higher power levels with less loss

Premium plug qualified for 22 awg horizontal cable patch cable: Protects performance integrity through the plug termination

Snagless plug design: Protects plugs when pulling through cable managers or pathways

Compatible with both T568A and T568B wiring: Provides universal wiring ability

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875961017	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Length US	25.0 FT	Cable Length	25 ft
-------------------	---------	--------------	-------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat5e	Wire Gauge	22 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 μ in Gold
Jacket Application	Plenum Rated	Bend Radius	0.94 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Solid	Operating Temperature Max	60 °C
Jacket Rating	CMP Rated	Cable Diameter	0.235 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C
