



Ortronics
PowerWise Cat5E solid cord Riser PVC, double ended 60ft, purple
Part No. PW5ER60DB-07



PWC5E PowerWise Cat5E UTP solid 22 awg conductor riser, double ended 60ft, purple

Features & Benefits

Each cord is factory tested: Ensures every cord shipped meets Category 5e component specifications

Larger 22 awg conductors: Support higher power levels with less loss

Premium plug qualified for 22 awg horizontal cable patch cable: Protects performance integrity through the plug termination

Snagless plug design: Protects plugs when pulling through cable managers or pathways

Compatible with both T568A and T568B wiring: Provides universal wiring ability

Specifications

General Info

| | | | |
|--------------|-----------|-------|--------|
| Product Line | Ortronics | Color | Purple |
|--------------|-----------|-------|--------|

| | | | |
|------------|--------------|-------------------|--------|
| UPC Number | 662875961666 | Country Of Origin | Mexico |
|------------|--------------|-------------------|--------|

| | | | |
|--------------------|------------------------|---------------|--------|
| Application Sector | Commercial, Industrial | Warranty Type | 5-Year |
|--------------------|------------------------|---------------|--------|

| | |
|------|-------------------|
| Type | Copper Patch Cord |
|------|-------------------|

Dimensions

| | | | |
|-------------------|---------|--------------|-------|
| Product Length US | 60.0 FT | Cable Length | 60 ft |
|-------------------|---------|--------------|-------|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|-----------------------------|---------------------------|---------------------------|----------------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
| Category Performance Rating | Cat5e | Wire Gauge | 22 AWG |
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 µ in Gold |
| Jacket Application | Riser Rated | Bend Radius | 0.94 in |
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
| Conductor Stranding | Solid | Operating Temperature Max | 60 °C |
| Jacket Rating | CMR Rated | Cable Diameter | 0.235 in |
| Braid | Non-braided Wiring | Operating Temperature | -10°-60°C |
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |
