



On-Q
12VDC 30W Power Supply
Part No. PW7725

Power your connected home devices with confidence using the 12VDC 30W Power Supply. This unit converts high voltage AC to low voltage DC, providing a stable and reliable power source. It's ideal for a wide range of applications, ensuring your devices run smoothly and efficiently.



Features & Benefits

Package includes a DC power supply with 2 ft barrel connector plug and a 1.5 ft AC power plug IEC C13/C14 connections
Stacks neatly in enclosure with AC1031 power strip

Specifications

General Info

Product Line	On-Q	UPC Number	804428028475
Country Of Origin	China	Application Sector	Residential
Standard	UL, cULus, CE, FCC, C-Tick, RoHS		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Output Voltage	12 V	Connection	DC Barrel
Amperage	2.5 A	Input Voltage	100 to 240 V

Environmental Conditions 10 to 90% (relative humidity, non-condensing)
