



Cisco QSFP-40G-CSR4 Compatible 40GBase-CSR4 QSFP+ Transceiver (MMF, 850nm, 400m, MPO/MTP, DDM, C-Temp)



## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers.

**99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page.

**98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875078319
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	18.3 mm	Product Depth US	72.4 mm
Product Height US	12.2 mm		

### Technical Information

Fiber Optic Cable Type	Multimode	Max Distance Support	400 m
Operating Temperature Min	0 °C	Operating Temperature Max	70 °C
Data Transfer Rate	42 Gbps	Connector Type	MPO
Form Factor	QSFP+		