



radiant Collection
radiant® 3.1A USB Outlet, Type C, 15A, Tamper-Resistant, Nickel
Part No. R26USBCCNICCV4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet features two USB Type-C connections to accommodate the latest mobile devices – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, this outlet offers accessible charging without sacrificing your plugs, and features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Accommodates the latest mobile devices with two built-in connections for the newer USB Type-C, which features a smaller, reversible connector and high-speed specs.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------------------------------|
| Product Line | Pass & Seymour | Color | Nickel |
| UPC Number | 785007180992 | Country Of Origin | China |
| Features | USB-C Charging | Outlet Type | Tamper-Resistant, USB-Charging |
| Application Sector | Residential | | |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.693 in | Product Depth US | 1.35 in |
|------------------|----------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.18 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|--------------|-------|----------------|---|
| USB Amperage | 3.1 A | Number of USBs | 2 |
|--------------|-------|----------------|---|

| | | | |
|------------------|------|----------|------|
| USB Power Output | 15 W | Amperage | 15 A |
|------------------|------|----------|------|

| | | | |
|----------------|--------|---------------|-----|
| Indoor/Outdoor | Indoor | Mounting Type | Box |
|----------------|--------|---------------|-----|
