



Six rear outlets, lighted switch, 15A. 6' (1.8m) cord. Perma Power computer grade, surge protection.

Features & Benefits

Six rear outlets, lighted switch, 15A. 15' (4.6m) cord. Perma Power computer grade, surge protection.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776043990
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA2	Type	PIOC

Dimensions

Product Width US	19.0 in	Product Weight US	3.1 lb
Product Height US	2.57 in	Product Length US	1.75 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single Stage	Connection	Cord-ended
Class	75	Amperage	15 A
Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]	Response Time	<1 ns
Mounting Type	Rack Mounting	Mounting	Yes
Type of Indicators	Light	Voltage	120.0 V